



Triple Crown Modular WaterFed® Pole

Effective January 30, 2017



Getting Started With Your Pole Operation and Maintenance Manual

Overview

Congratulations on your purchase.

Thank you for selecting a Triple Crown Modular WaterFed® Pole. Built with high quality materials and featuring industry leading technology, we are sure that you'll enjoy your new pole. This guide will run you through the basic dos and don'ts of your pole along with instructions for setting it up out of the box.

CAUTION



**DO NOT
USE NEAR
ELECTRICITY!**

CAUTION



**DO NOT
STEP ON
SECTIONS!**

CAUTION



**DO NOT
DROP POLE!**

In The Box

Parts Check

- Triple Crown Modular WaterFed® Pole
- Brush
- Pole Tubing w/ Pole Connector
- Double Plastic Angle Adaptor
- Shut-Off Valve
- PTFE Lubricant
- End Plug
- Pole Bag

1. Unpacking/Inspecting The Pole


Carefully remove the packaging material from around your pole and discard. Examine all collars and sections to make sure that nothing was damaged in shipping. If damage has occurred, notify abc Window Cleaning Supply within 48 hours.

2. Initial Setup

You can watch the video at:
www.abcWindowSupply.com/ModularGuide



1. Separate all sections. Some may be stored inside of each other.
2. Screw double angle adaptor onto the end of your number one section.
3. Screw brush onto the euro threaded side of your double angle adaptor.
4. Assemble sections in order (section 1 to section 2, section 2 to section 3, etc.). Use light coat of PTFE spray on each connection before every use.
5. Insert End Plug into the last section you are using to protect the pole end.
6. Insert pole tubing into desired fitting on your brush. We suggest that you run your tubing externally.



3. Replacement Parts

Single Jetted Brush - WF50465-PJ2
 Double Jetted Brush - WF50465-FJ1
 Double Angle Adaptor - TCSWITCH
 Tip - 6000-G-1Tip
 #1 Section Collar - 6000-G-RC1
 Bag - 5000-BAG
 End Plug - 5000-PLUG
 PTFE Can - 5000-PTFE
 Section - 5000-[x]-RS
 Shut-Off Valve - WF601311
 Tubing - WF600600-[x]

Optional Accessories

Carbon Gooseneck - 6000-G-GN[x]-CF

